

Contenance des tourets

Tourets Type "METROPOLE" Cerclés								
Type	CBM	DBM	EBM	FBM	GBM	HBM	IBM	JBM
Garde approx mm	30	30	30	50	80	80	80	80
Diamètre du câble mm	contenance m							
6	6 989	/	/	/	/	/	/	/
8	3 931	/	/	/	/	/	/	/
10	2 516	3 296	4 488	/	/	/	/	/
12	1 747	2 289	3 117	5 486	9 764	/	/	/
14	1 284	1 681	2 290	4 031	7 173	10 449	/	/
16	983	1 287	1 753	3 086	5 492	8 000	/	/
18	777	1 017	1 385	2 438	4 339	6 321	10 667	12 960
20	629	824	1 122	1 975	3 515	5 120	8 640	10 500
22	520	681	927	1 632	2 905	4 231	7 140	8 676
24	437	572	779	1 372	2 441	3 556	6 000	7 294
26	372	488	664	1 169	2 080	3 030	5 112	6 212
28	321	420	572	1 008	1 793	2 612	4 408	5 356
30	280	366	499	878	1 562	2 276	3 840	4 666
32	246	322	438	772	1 373	2 000	3 375	4 101
34	218	285	388	683	1 216	1 772	2 990	3 633
36	194	254	346	610	1 085	1 580	2 667	3 240
38	174	228	311	547	974	1 418	2 393	2 908
40	157	206	281	494	879	1 280	2 160	2 625
42	143	187	254	448	797	1 161	1 959	2 380
44	130	170	232	408	726	1 058	1 785	2 170
46	119	156	212	373	664	968	1 633	1 985
48	109	143	195	343	610	889	1 500	1 823
50	101	132	180	316	562	819	1 382	1 680
52	/	122	166	292	520	757	1 278	1 553
54	/	113	154	271	482	702	1 185	1 440
56	/	105	143	252	448	653	1 102	1 339
58	/	98	133	235	418	609	1 027	1 248
60	/	92	125	219	391	569	960	1 166
62	/	86	117	206	366	533	899	1 092
64	/	80	110	193	343	500	844	1 025
66	/	/	103	181	323	470	793	964
68	/	/	97	171	304	443	747	908
70	/	/	92	161	287	418	705	857
72	/	/	87	152	271	395	667	810
74	/	/	82	144	257	374	631	767
76	/	/	78	137	243	355	598	727
78	/	/	74	130	231	337	568	690
80	/	/	70	123	220	320	540	655
82	/	/	/	/	209	305	514	625
84	/	/	/	/	199	290	490	595
86	/	/	/	/	190	277	467	568
88	/	/	/	/	182	264	446	542
90	/	/	/	/	174	253	427	518
92	/	/	/	/	/	242	408	496
94	/	/	/	/	/	232	391	475
96	/	/	/	/	/	222	375	456

Tourets Type "PERDUS"							
Type	WBP	XBP	ABP	BBP	CBP	DBP	EBP
	idem WCP	Idem XCP	idem ACP				
Garde approx mm	20	25	30	40	50	50	50
Diamètre du câble mm	contenance m						
6	1 660	2 833	4 917	7 010	9 208	/	/
8	934	1 594	2 766	3 945	5 180	9 010	
10	598	1 020	1 770	2 524	3 315	5 740	7 636
12	415	708	1 229	1 753	2 300	4 010	5 303
14	305	520	903	1 288	1 690	2 946	3 896
16	233	398	691	986	1 295	2 256	2 983
18	184	315	546	779	1 023	1 782	2 357
20	149	256	443	631	829	1 444	1 909
22	/	211	366	521	684	1 193	1 578
24	/	/	307	438	575	1 003	1 326
26	/	/	262	373	490	854	1 130
28	/	/	/	322	423	737	974
30	/	/	/	280	368	642	848
32	/	/	/	/	324	564	746
34	/	/	/	/	287	500	661
36	/	/	/	/	/	446	589
38	/	/	/	/	/	400	529
40	/	/	/	/	/	361	477
42	/	/	/	/	/	/	433
44	/	/	/	/	/	/	394
46	/	/	/	/	/	/	361
48	/	/	/	/	/	/	331
50	/	/	/	/	/	/	305

Tourets Type "EXPORT"											
Type	XBE	ABE	BBE	CBE	DBE	EBE	FBE	GBE	HBE	IBE	IBE
Garde approx mm	30	30	30	50	80	80	80	80	100	80	80
Diamètre du câble mm	contenance m										
6	1 595	4 580	6 520	/	/	/	/	/	/	/	/
8	890	2 570	3 655	5 830	/	/	/	/	/	/	/
10	565	1 640	2 330	3 720	4 090	5 570	/	/	/	/	/
12	390	1 135	1 615	2 580	2 830	3 860	/	/	/	/	/
14	285	830	1 180	1 890	2 075	2 825	/	/	/	/	/
16	220	635	900	1 445	1 585	2 160	/	/	/	/	/
18	170	500	710	1 135	1 250	1 700	2 460	/	/	/	/
20	140	405	570	920	1 010	1 375	1 990	/	/	/	/
24	95	280	395	635	695	950	1 375	2 110	/	/	/
28	/	205	290	465	510	695	1 005	1 545	2 495	/	/
32	/	155	220	355	390	530	765	1 180	1 905	/	/
36	/	120	170	280	305	415	600	925	1 500	/	/
40	/	/	140	225	245	335	485	750	1 210	/	/
44	/	/	115	185	200	275	400	615	1 000	/	/
48	/	/	/	155	170	230	335	515	835	/	/
52	/	/	/	130	145	195	280	435	710	/	/
56	/	/	/	/	125	165	240	375	610	/	/
60	/	/	/	/	/	145	210	325	530	/	/
64	/	/	/	/	/	/	185	285	465	/	/
68	/	/	/	/	/	/	160	250	410	/	/
72	/	/	/	/	/	/	/	225	365	/	/
76	/	/	/	/	/	/	/	200	325	/	/
80	/	/	/	/	/	/	/	/	290	/	/
84	/	/	/	/	/	/	/	/	265	/	/
88	/	/	/	/	/	/	/	/	240	/	/
92	/	/	/	/	/	/	/	/	220	/	/

Ces 3 tableaux sont valables pour les câbles BT.

Pour les câbles HTA, il faut s'assurer que le tambour du touret est compatible avec le rayon de courbure du câble.